



BETA 7204BP
BASIC PLUS leather ankle shoe,
smooth-finished, water-repellent,
with front protection



Certifications and Standards

CE S3S FO SR HRO RS EN ISO 20345:2022

Features

The 7204B metal-free shoe with HRO rubber outsole and front protection flap provides maximum strength and protection at an excellent price-performance ratio.

FIRST PRICE METAL FREE

The 7204BP provides protection without metal parts, offering greater comfort and versatility of use, at a competitive price.

WIDE FOOTBED

The wide fit further enhances the comfort of the shoe, preventing possible constriction of the foot at any time of day.

NEW STANDARD EN ISO 20345:2022+A1:2024

The shoe is S3S FO SR RS certified according to the latest EN ISO 20345:2022+A1:2024 standard. It is ideal for even the most demanding working environments, thanks to improved slip, oil and penetration resistance.



PROTECTIVE FLAP

The double-tear flap ensures stability, protecting the foot from slag, debris and external agents while working.



MAXIMUM RESISTANCE

The rubber outsole makes the shoe extremely durable and heat-resistant up to 300°C.



Certifications and Standards

CE S3S FO SR HRO RS EN ISO 20345:2022



Specifications

LACING: traditional
 WEIGHT (INDICATIVE SIZE 42): 675 g
 TYPE: high

Lightness

Smooth-finished, water-repellent leather with front protection

Comfort

Rubber resistant to up to 300 °C (HRO)



Safety

Polyurethane foam

Protections

Tip: Polymer material, 200 joules
 Durability: Composite fibre, ceramic treatment

Coded items

	Art.	EU	UK	 mm
072040635	7204BP 35	35	2,5	230
072040636	7204BP 36	36	3,5	237
072040637	7204BP 37	37	4,5	244
072040638	7204BP 38	38	5	251
072040639	7204BP 39	39	6	258
072040640	7204BP 40	40	6,5	265
072040641	7204BP 41	41	7	272
072040642	7204BP 42	42	8	279
072040643	7204BP 43	43	9	286
072040644	7204BP 44	44	10	293
072040645	7204BP 45	45	10,5	300
072040646	7204BP 46	46	11	307
072040647	7204BP 47	47	12	314
072040648	7204BP 48	48	13	321

Scan the QR Code to access the web tab

Specs, media and documentation in one click.

