

USB 10 Gbps 2 Port USB Type-A + 2 Port USB Type-C™ Hub with USB Type-C™ connector and additional power port

Description

This solid USB hub by Delock with metal housing can be connected to a computer, laptop or mobile device via the **USB Type-C™** interface. It has **two USB Type-A connectors** as well as **two USB Type-C™ connectors**. Different USB devices such as USB flash memory, card reader, external enclosure etc. can be connected.

Small, stable and handy

Due to its **small dimensions and its sturdy housing**, this Delock hub is particularly suitable for travelling. It can simply be packed into the bag together with the laptop or tablet and used as needed.

Additional USB Type-C™ connector for power supply

If the power supply of the host device is insufficient, a **separate power supply can be connected to the additional USB-C™ female** to supply the peripherals with up to **5 V and 3 A**. Charging of the host device is not possible.



Item no. 64299

EAN: 4043619642991

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 2 x USB 10 Gbps USB Type-C™ female
 - 2 x USB 10 Gbps Type-A female
 - 1 x USB Type-C™ female (optional for power supply, max. 5 V / 3 A)
- Chipset: VIA VL822
- Data transfer rate up to 10 Gbps
- 1 x LED indicator
- Robust metal housing
- Cable length: ca. 30 cm
- Colour: grey
- Plug & Play
- Dimensions (LxWxH): ca. 115 x 37 x 13 mm

System requirements

- Android 14.0 or above
- Chrome OS
- Linux Kernel 6.2 or above
- Mac OS 14.2.1 or above
- Windows 10/10-64/11
- iPad Air (4th Generation) or above
- iPad Pro (3rd Generation) or above
- Surface Pro 7
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 or Thunderbolt™ 4 port

Package content

- Hub USB 10 Gbps
- User manual

Images



General

Function:	Plug & Play
Supported operating system:	Chrome OS Surface Pro 7 Windows 10 32-Bit Windows 10 64-Bit iPad Pro (3rd Generation) or above iPad Air (4th Generation) or above Windows 11 Linux Kernel 6.2 or above Android 14.0 or above Mac OS 14.2.1 or above
LED indicator:	1 x

Interface

Connector 1:	1 x USB 10 Gbps USB Type-C™ male
Connector 2:	2 x USB 10 Gbps USB Type-C™ female
Connector 3:	2 x USB 10 Gbps Type-A female
Connector 4:	1 x USB Type-C™ female (optional for power supply, max. 5 V / 3 A)

Technical characteristics

Chipset:	VIA VL822
Data transfer rate:	10 Gbps

Physical characteristics

Housing material:	metal
Cable length:	30 cm
Length:	115 mm
Width:	37 mm
Height:	13 mm
Colour:	grey

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de