

DisplayPort 1.4 Cable 8K 30 Hz male to female 1 m panel-mount black

Description

This cable by Delock can be used to extend a DisplayPort connection and to connect various devices. The female port can be attached with two screws, e.g. to a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a DisplayPort connector in an easily accessible position.



Item no. 87825

EAN: 4043619878253

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x DisplayPort female
1 x DisplayPort male
- Resolution up to 7680 x 4320 @ 30 Hz (depending on the system and the connected hardware)
- Supports HDCP 2.2 (High-Bandwidth Digital Content Protection)
- Supports HDR
- Transmission of audio and video signals
- Material: PC plastic
- Mounting hole: ca. 21.5 x 12.5 mm, screw hole pitch ca. 28 mm
- Cable gauge: 30 AWG
- Cable diameter: ca. 6 mm
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort panel-mount cable

Images



Interface

Connector 1:	1 x DisplayPort female
Connector 2:	1 x DisplayPort male

Technical characteristics

Maximum screen resolution:	7680 x 4320 @ 30 Hz
----------------------------	---------------------

Physical characteristics

Length:	1 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de