

414/SP

Set of ground drills coated with TiN in drawers

- HSS steel
- Short series
- TiN coated
- $R \leq 900 \text{ N/mm}^2$.
- HV 0.05 ≥ 2500

	Art.		 g
004140419	414/SP19	set of twist drills with cylindrical shanks (item 414) in case $\varnothing 1 \div 10 \times 0,5 \text{ mm}$	
004140425	414/SP25	set of twist drills with cylindrical shanks (item 414) in case $\varnothing 1 \div 13 \times 0,5 \text{ mm}$	1,1
004140429	414/SP49	set of twist drills with cylindrical shanks (item 414) in case $\varnothing 1 \div 13 \times 0,25 \text{ mm}$	2,5
004140430	414/SPV4	empty case for item 414/SP49	
004100427		Case for items 410/SP25, 412/SP25, 414/SP25, 415/P25, empty	
004100421		Case for items 410/SP19, 412/SP19, 414/SP19, 415/SP19, 415CO/SP19, 416/SP19, empty	



Scan the QR Code to access the web tab
Specs, media and documentation in one click.

