

Product Datasheet

Item No.: 823320

as
Schwabe
TechnikProdukte

PRODUCT NAME

IronCoat Xperts metal cable reel 40 m H07RN-F 3G2,5 IP44 "F"



- Reel body made from hot-dip-galvanized steel plate with patented protective insulation
- With ergonomic non-slip 2-component handle and cable guide
- With built-in thermal circuit breaker
- IP44: protected against foreign bodies and splash-proof
- With stable, shock-absorbing X double-tube frame with star-grip brake
- With safety plug
- With 3 shock-proof socket outlets
- With integrated voltage indicator
- 230 V, 16 A, max. 3,500 W

Reference image

Technical data

EAN	4059948004003
Weight [kg]	11.5
Dimensions	22x42,6x32,5 cm
Main color	silver
Series	IronCoat Xperts
Category	Cable reels
Subcategory	Metal cable reels
Cable type	H07RN-F
Cross section [mm ²]	3G2,5
Cable color	black
Cable length [m]	40
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
Brake	Yes
Drum diameter	320 mmØ
Metal frame	Yes
Thermal fuse	1P
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44 with 40 m H07RN-F 3G2,5
Output	3x shock-proof connector with blue protective cap, socket insert, 230 V, 16 A, IP44 "F"
Total number of sockets	3
Number of Type E sockets (230 V)	3
Number of cores	3

Your partner for professional lighting and electrical products.