

# Delock Cable USB 2.0 Micro-B female panel-mount > USB 2.0 Type-A female panel-mount 25 cm

## Description

This cable enables you to extend a USB 2.0 connection and can be used to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. This can be used to install an USB connector on an easily accessible position.



**Item no. 85109**

EAN: 4043619851096

Country of origin: China

Package: Zip poly bag

## Technical details

- Connector:  
USB 2.0 Type Micro-B female with screw nuts for installation >  
USB 2.0 Type-A female with screw nuts for installation
- Screw type: #4-40 UNC
- Mounting hole Type Micro-B ca. 8 x 3 mm, screw hole pitch ca. 30 mm
- Mounting hole Type-A ca. 15 x 8 mm, screw hole pitch ca. 30 mm
- Data transfer rate up to 480 Mbps
- Cable gauge: 28 AWG data line  
28 AWG power line
- Cable diameter: ca. 3.8 mm
- Colour: black
- Length incl. connector: ca. 25 cm

## System requirements

- A free USB port

## Package content

- USB panel-mount cable
- 4 screws

---

## Images



## General

Specification:	USB 2.0
----------------	---------

## Interface

Connector 1:	1 x USB 2.0 Type-A female for installation
Connector 2:	1 x USB 2.0 Type Micro-B female for installation

## Technical characteristics

Data transfer rate:	480 Mbps
---------------------	----------

## Physical characteristics

Cable gauge:	28 AWG data line 28 AWG power line
Screw distance:	30 mm
Screw type:	#4-40 UNC
Length:	0.25 m
Colour:	black
Cable diameter:	3.8 mm

## Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de