




P/N LEGEND

<u>A2004</u>	<u>H-2XNP</u>	<u>N</u>	<u>0</u>	<u>X</u>	<u>NP</u>	<u>N</u>	<u>00</u>	<u>G</u>	
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩
① Series No.									
② Connector type: H=Housing									
③ No. of circuits									
④ N=Halogen Free									
⑤ Material: 0=Nylon 66-V0									
⑥ Color: W=White; B=Black									
⑦ Plating code: NP=Non-plating									
⑧ Plating code: N=Non-plating									
⑨ Option code: 00=Standard									
⑩ Packing code: G=Bag									

SPECIFICATIONS
Current Rating: 3A AC,DC
Voltage Rating: 250V AC,DC
Temperature Range: -40°C ~ +105°C
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 800V AC/minute

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
2X02P	2.00	5.90	2X13P	24.00	27.90
2X03P	4.00	7.90	2X14P	26.00	29.90
2X04P	6.00	9.90	2X15P	28.00	31.90
2X05P	8.00	11.90	2X16P	30.00	33.90
2X06P	10.00	13.90	2X17P	32.00	35.90
2X07P	12.00	15.90	2X18P	34.00	37.90
2X08P	14.00	17.90	2X19P	36.00	39.90
2X09P	16.00	19.90	2X20P	38.00	41.90
2X10P	18.00	21.90	2X22P	42.00	43.90
2X11P	20.00	23.90	2X23P	44.00	45.90
2X12P	22.00	25.90	2X24P	46.00	47.90

							燦達電子工業股份有限公司	
					JOINT TECH ELECTRONIC IND. CO., LTD.			
					UNIT	SCALE	SHEET	TITLE: 2.00mm PITCH HOUSING
					mm	1 : 1	1 of 1	
					DRAWN BY		APPROVED BY	
					劉建芳		謝瑞清	
					2016.06.15		2016.06.15	
					GENERAL TOLERANCE			
A1	EN202508062039	2025.08.06	吳清	X. X±0.25	ANGLE±			
A0	NEW RELEASE	2016.06.15	劉建芳	X. XX±0.15			DRAW NO. :	
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05			A2004H-2XNPN0XNPN00G	
							REV. A1	