

Premium HDMI Cable 4K 60 Hz 1 m

Description

This certified premium HDMI cable by Delock can be used to connect devices with an HDMI interface, such as televisions, Blu-ray players, monitors or projectors. By supporting a maximum bandwidth of 18 Gbps, content can be displayed with resolutions of up to 4K Ultra HD (3840 x 2160 @ 60 Hz).

Versatile due to highly flexible cable material

The cable is particularly characterised by its small diameter and the highly flexible cable material, making it particularly easy to install.



Item no. 85215

EAN: 4043619852154

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x HDMI-A male >
 - 1 x HDMI-A male
- Certified Premium HDMI cable
- High Speed HDMI with Ethernet (HEC) specification
- Cable gauge: 34 AWG
- Cable diameter: ca. 4.5 mm
- Twisted-pair cabling
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 18 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- 3D support: up to 1920 x 1080 @ 60 Hz; 3840 x 2160 @ 30 Hz
(depending on the system and the connected hardware)
- Supports the 21:9 cinema aspect ratio
- Supports 1080p HFR (High Frame Rate) 3D
- Up to 120 Hz refresh rate
- Supports transmission of 2 video channels simultaneously to use one display for two viewers
- Supports colour sampling in 4:2:0 format (original format of Blu-Ray, DVD and TV)
- Contains Audio Return Channel (ARC)
- Up to 32 audio channels for speakers

- Up to 1536 kHz audio sampling rate
- Supports transmission of up to 4 audio channels simultaneously
- Supports dynamic adjustment of lip synchronicity for audio / video delays
- Supports CEC 2.0 control commands
- Supports Dolby® TrueHD and DTS-HD Master Audio™
- Supports HDR
- More lively and natural colours
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- A free HDMI-A interface

Package content

- Premium HDMI cable

Images



General

Specification:	HDMI 2.0
Style:	both sides identical

Interface

Connector 1:	1 x HDMI-A male
Connector 2:	1 x HDMI-A male

Technical characteristics

Data transfer rate:	up to 18 Gb/s
Maximum screen resolution:	3D: 3840 x 2160 @ 30 Hz 3840 x 2160 @ 60 Hz
Maximum refresh rate:	120 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	34 AWG
Shielding:	triple
Length:	1 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de