

Product Datasheet

Item No.: 23240

PRODUCT NAME

Xperts extension reel with 3-way IP44 socket 50 m H07RN-F 3G1,5 IP44



- Reel body made from robust, shatter-proof special plastic with cable reel
- With stable, shock-absorbing X double-tube frame with star-grip brake
- Frame with ergonomic non-slip 2-component handle and cable guide
- With built-in thermal circuit breaker
- Perfect for roofing and scaffolding work
- Solid rubber 3-way connector for shock-proof plugs with 360° rotating safety flap lids
- With 1.5 m power cord with shock-proof plug
- Cable in red safety color
- IP44: protected against foreign bodies and splash-proof
- 230 V, 16 A, max. 3,500 W

Reference image

Technical data

| | |
|----------------------------------|---|
| EAN | 4011160232404 |
| Weight [kg] | 7.75 |
| Dimensions | 22x42,6x32,5 cm |
| Main color | black |
| Series | Xperts |
| Category | Cable reels |
| Subcategory | Extension reels |
| Cable type | H07RN-F |
| Cross section [mm ²] | 3G1,5 |
| Cable color | red |
| Cable length [m] | 50 |
| Rated voltage [V] | 230 |
| Rated current [A] | 16 |
| Maximum power | 3500 W |
| Brake | Yes |
| Drum diameter | 320 mmØ |
| Metal frame | Yes |
| Thermal fuse | 1P |
| IP protection | IP44 |
| Input | Shock-proof plug 230 V, 16 A, IP44 with 50 m H07RN-F 3G1,5 |
| Output | 3x rubber shock-proof connector with protective cap 230 V, 16 A, IP44 |
| Total number of sockets | 3 |
| Number of Type F sockets (230 V) | 3 |
| Number of cores | 3 |

Your partner for professional lighting and electrical products.