




Transfer or duplication of this document as well as the utilisation or communication of its content are not permitted unless express consent is granted. Violations give rise to claims for damages. All rights reserved in case of patent, utility model or design patent registrations.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Designeintragung vorbehalten.



- General Information
- 1. ME 45 UT
 - 2. Foot catch
 - 3. Marking area
 - 4. PCB guidance
 - 5. FE contact
 - 6. ME BUS 22,5 MC 2
 - 7. ME BUS 22,5 MC 10
 - 8. Mounting rail like EN 60715: TH 35-7,5/15 or mounting rail TH 35-15x1,5 similar to EN 60715
- ⊕ = Workpiece zero point for mechanical processing
- Simplified representation, exemplary shown in gray
 - Document excluded from change process
 - CAD Data see Download-Center on www.phoenixcontact.com
 - Linear dimensions [mm]
 - Tolerances apply in a normal climate according to DIN EN ISO 291-23/50-2, PA plastic parts with about 2% (% by weight) moisture content.
 - Recommended PCB outline on www.phoenixcontact.com webcode: #0512

schematic symbol	description	electrical symbol
P	parallel	
SE	serial	

 DIN A3		document-No. / RI 00858563 / 02		date 05.01.2026	scale 1:1
		ident.-No. 2201342	document-type TECDOC 2D_Productdrawing		
		description ME 45 UT/FE BUS/10+2 BUGY			
		page 1	of 1		