

Product Datasheet

Product code: LE-HHUVWE

Product type: Loupes and Magnifiers

Made in: China

Description: Ideal-tek LE-HHUVWE hand-held wide view UV magnifier combines functionality and precision with a rectangular glass lens, complemented by a spot lens with 4x magnification, and UV & White LEDs. Operating at 365nm, the UV LEDs provide exceptional brightness to highlight fluorescing objects such as paper, ink, circuit boards, currency, and more. The White LEDs offer two brightness levels, ensuring versatility across various applications. Its high-quality rectangular lens delivers 2.25x magnification, complemented by a 1" diameter spot lens with 4x magnification. ESD Safe, this magnifier is perfect for applications in Industrial Inspection to detect defects with accuracy, Dermatology, Trauma, Schools, Ophthalmology, Forensic Science, Hospitality/Food Industry, Agriculture, and more.

Special features: 18 White + 26 UV LEDs - 5V/1A, USB Type-C

Picture:



Product dimensions:	OAL	218.0 mm – 8.583 inch
	Width	138.0 mm – 5.433 inch
	Height	37.0 mm – 1.457 inch