

Product Datasheet

Item No.: 10270

PRODUCT NAME

CEE camping cable reel with USB Ø 285 mm 25 m H07BQ-F 3G2.5 IP44



Reference image



- cable reel body made of durable, highly impact-resistant special plastic
- with a robust, shock-absorbing galvanised single-frame base with parking brake
- with thermal cut-out and cable guide
- with orange warning-coloured polyurethane BQ-F cable
- includes a cable clip for securing the cable to the housing
- suitable for continuous outdoor use
- products tested in accordance with EN 61242, DIN VDE 0620-2-1, DIN EN 50525-2, IEC 60309
- IP44: protected against solid foreign objects and water splashes
- with ergonomic handle
- with CEE plug 230 V, 16 A, 3P with Powerlight voltage indication
- 2 × earthed sockets 230 V with hinged safety flaps and hammer symbol – increased durability
- 1 × CEE socket with hinged flap 230 V, 16 A, 3P
- 2 × USB ports (1 × Type A, 1 × Type C)

Technical data

EAN	4011160102707
Weight [kg]	5.77
Main color	orange
Series	PowerLight
Category	Camping and caravanning
Subcategory	Extensions
Cable type	H07BQ-F
Cross section [mm²]	3G2.5
Cable color	orange
Cable length [m]	25
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500
Thermal fuse	Termik 1P
IP protection	IP44
Total number of sockets	3
Number of Type F sockets (230 V)	2
Number of CEE 230 V sockets	1
Number of cores	3

Your partner for professional lighting and electrical products.