

Product Datasheet

Item No.: 60454



PRODUCT NAME

Extension with 3-way socket outlet 4,5 m H07RN-F 3G1,5 IP44



Reference image



- Approved for use on construction sites and in agricultural applications
- IP44: protected against foreign bodies and splash-proof
- Heavy-duty design made from solid rubber
- Approved for use on construction sites and in agricultural applications
- With eyelets for suspension
- With shock-proof plug and rotating, self-locking safety flap lids with hammer symbol
- 230 V, 16 A

Technical data

EAN	4011160604546
Weight [kg]	1.1
Dimensions	20x7x20 cm
Main color	black
Category	Extensions
Subcategory	For use on construction sites
Cable type	H07RN-F
Cross section [mm²]	3G1,5
Cable color	black
Cable length [m]	4.5
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44
Output	3x rubber shock-proof connector with protective cap 230 V, 16 A, IP44
Total number of sockets	3
Number of Type F sockets (230 V)	3

Your partner for professional lighting and electrical products.

