

# Product Datasheet

Item No.: 23994

PRODUCT NAME

## IronCoat Xperts CEE metal cable reel 40 m H07BQ-F 5G1,5 IP44



Reference image



- Reel body made from hot-dip-galvanized steel plate with patented protective insulation
- With ergonomic non-slip 2-component handle and cable guide
- With built-in thermal circuit breaker
- IP44: protected against foreign bodies and splash-proof
- With stable, shock-absorbing X double-tube frame with star-grip brake
- With CEE plug 400 V, 16 A, 5-pole
- With 2 shock-proof socket outlets 230 V, splash-proof and 1 CEE socket 400 V, 16 A, 5-pole
- CEE 400 V, 16 A, 5-pole, max. 10,000 W

### Technical data

EAN	4011160239946
Weight [kg]	10.6
Dimensions	25,6x42,6x32,5 cm
Main color	silver
Series	IronCoat Xperts
Category	Cable reels
Subcategory	Metal cable reels
Cable type	H07BQ-F
Cross section [mm <sup>2</sup> ]	5G1,5
Cable color	orange
Cable length [m]	40
Rated voltage [V]	400
Rated current [A]	16
Maximum power	11 kW
Brake	Yes
Drum diameter	320 mmØ
Metal frame	Yes
Thermal fuse	3P
IP protection	IP44
Input	CEE plug 400 V, 16 A, 5-pole with 40 m H07BQ-F 5G1,5
Output	2x shock-proof socket outlet with red cover 230 V, 16 A, IP44 1x CEE socket 400 V, 16 A, 5-pole
Total number of sockets	3
Number of Type F sockets (230 V)	2
Number of CEE 400 V 16 A sockets	1
Number of cores	5

Your partner for professional lighting and electrical products.