

Flat suction cup (round)

SUF 6 NBR-55 SC020

Part no.:10.01.01.13941

<https://www.schmalz.com/10.01.01.13941>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 6 NBR-55 SC020

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 6

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d1	4.70 mm
d	3.10 mm
Dk	6.70 mm
Dmax(S)	6.80 mm
Ds	6 mm
H	5.50 mm
H2	2.30 mm
H3	3 mm
Z (Stroke)	0.60 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	1.40 N
Pull-off force	1.40 N
Volume	0.02 cm ³
Curve radius (min) (convex)	8 mm
Size	6
Nipple family	SC020
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	0.20 g

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SUF 6 NBR-55 SC020

Part no.:10.01.01.13941

<https://www.schmalz.com/10.01.01.13941>

Product family

SUF

Accessories



SC 020 M5-AG

Part no.:10.01.06.04273

Connection geometry: 020

Vacuum connection: M5-M

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm



SC 020 M5-IG

Part no.:10.01.06.04306

Connection geometry: 020

Vacuum connection: M5-F

Fitting length: 8.7 mm

Nominal diameter dn: 1.8 mm

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl