



## Mi TS 60

- DIN rail
- DIN rail 35 x 15 mm, 584 mm long

### CONNECTION DATA

### MECHANICAL PROPERTIES

Delivered accessories: Fastening material  
Suitable for box size: 4, 6, 8

### AMBIENT CONDITIONS

Application area: Indoor installation  
Maximum ambient temperature 24 h: 35 °C  
Ambient temperature: -5 °C up to +40 °C  
Relative humidity: ≤ 50 % at 40 °C, ≤ 100 % at 25 °C

### MATERIAL PROPERTIES

Material: Steel  
Surface treatment: Sendzimir galvanised

### DIMENSIONS

Height: 15 mm  
Width: 35 mm  
Depth: 584 mm  
Net weight: 0.398 kg  
Length: 584 mm  
Material thickness: 1.5 mm

### CERTIFICATES

conforming to the standards: DIN EN 60715, IEC 61439-2

## SALES DATA

Product number: 2000024  
EAN: 4012591650249  
Pack unit: 1  
Customs tariff number: 85371098  
ETIM class: DYNAMIC: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-9.0: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-8.0: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-7.0: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-6.0: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-5.0: EC001285 - Mounting rail for electrical/industrial control equipment  
ETIM-4.0: EC001285 - Mounting rail for electrical/industrial control equipment

## DRAWINGS

