




DIN 964 A

~ISO 2010

4.8

Norma ritirata



BN 368

Viti a testa svasata con calotta

ed intaglio

Acciaio 4.8

zincato bianco

- ~UNI 6110
- ~ČSN 021155

[3D Cadenas](#)

Tutte le misure con filettatura quasi completa

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1146297	M2	3,8	1,2	0,5	0,8	4
1146300						5
1146319						6
1146327						8
1146335						10
1146505	M2,5	4,7	1,5	0,6	1	4
1146513						5
1146521						6
1146548						8
1146556						10
1146564						12
1146580						16
1146602						20
1146777	M3	5,6	1,65	0,8	1,2	4
1146785						5
1146793						6
1146807						8
1146815						10
1146823						12
1146831						(14)
1146858						16
1146874						20
1146890						25
1146904						30
1146912						35
1146920						40

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1146955	(M3,5)	6,5	1,93	0,8	1,4	8
1146963						10
1146971						12
1146998						(14)
1147005						16
1147021						20
1147099	M4	7,5	2,2	1	1,6	5
1147102						6
1147110						8
1147129						10
1147137						12
1147145						(14)
1147153						16
1147161						(18)
1147188						20
1147218						25
1435450						(28)
1147226						30
1147234						35
1147242						40
1147250						45
1147269						50
1471511						60
1471538						70
1471546						80
1147277	M5	9,2	2,5	1,2	2	6
1147285						8
1147293						10
1147307						12
1147315						(14)
1147323						16
1147358						20
1147374						25
1147382						30
1147390						35
1147404						40
1147412						45
1147420						50
1147439						60
1471554						70
1471562						80

Article#	d ₁	d ₂ max.	k max.	n	t min.	L
1471570	M5	9,2	2,5	1,2	2	90
1471589						100
1147447	M6	11	3	1,6	2,4	8
1147455						10
1147463						12
1147471						(14)
1147498						16
1147501						(18)
1147528						20
1147544						25
1147552						30
1147560						35
1147579						40
1147587						45
1147595						50
1147609						60
1435485						70
1471597						80
1471600						90
1471619						100
3056169	M8	14,5	4	2	3,2	12
1122142						16
1122177						20
1122193						25
1122207						30
1122215						35
1122223						40
1122258						50
1122266						60
1122274						70
1471627						80