

Product Datasheet

Item No.: 860381

as
Schwabe
TechnikProdukte

PRODUCT NAME

Rubber extension for construction site 1-way 20 m H07RN-F 3G2,5 IP44 "F"



**DGUV-I
203-006**
FORMERLY
BGI 608

- Approved for use on construction sites and in agricultural applications
- IP44: protected against foreign bodies and splash-proof
- Approved for use on construction sites and in agricultural applications
- Shock-proof plug and shock-proof connector with protective cap
- 230 V, 16 A

Reference image

Technical data

EAN	4059948001743
Weight [kg]	4.6
Dimensions	25x10x25 cm
Main color	black
Category	Extensions
Subcategory	For use on construction sites
Cable type	H07RN-F
Cross section [mm ²]	3G2,5
Cable color	black
Cable length [m]	20
Rated voltage [V]	230
Rated current [A]	16
Maximum power	3500 W
IP protection	IP44
Input	Shock-proof plug 230 V, 16 A, IP44
Output	1x shock-proof connector with protective cap 230 V, 16 A, IP44 "F"
Total number of sockets	1
Number of Type E sockets (230 V)	1
Number of cores	3

Your partner for professional lighting and electrical products.