

PI6W-1P ❼

For RM699BV, RSR30


Screw terminals
Max. tightening moment for the terminal: 0,3 Nm
35 mm rail mount
acc. to EN 60715
98,5 x 6,2 x 85,5 mm
One pole
6 A, 250 V AC



Connection diagram



Dimensions



Accessories ❾



ZG20


PI6W-1246


PI6W-1P ❽

For RM699BV


Screw terminals
Max. tightening moment for the terminal: 0,3 Nm
35 mm rail mount
acc. to EN 60715
98,5 x 6,2 x 85,5 mm
One pole
6 A, 250 V AC




Connection diagram



Dimensions



Accessories ❾



ZG20


PI6W-1246


PI6W-1PS ❽

For RM699BV, RSR30


Screw terminals
Max. tightening moment for the terminal: 0,3 Nm
35 mm rail mount
acc. to EN 60715
98,5 x 6,2 x 85,5 mm
One pole
6 A, 250 V AC



Connection diagram



Dimensions



Accessories ❾



ZG20


PI6W-1246


PI6WB-1PS ❽

For RM699BV, RSR30


Spring terminals
35 mm rail mount
acc. to EN 60715
98,3 x 6,2 x 84,6 mm
One pole
6 A, 250 V AC




Connection diagram



Dimensions



Accessories ❾


ZG20


PI6W-1246

❼ Sockets without electronic. ❽ Sockets with electronic PI6W., 6W.: version codes and selection of relays for sockets can be found in the data sheets of interface relays PIR6W., SIR6W. - see www.relpol.com.pl ❾ Colours of strips: ZG20-1, JB20-1 red; ZG20-2, JB20-2 black; ZG20-3, JB20-3 blue.

28.12.2023

Export Sales Department phone +48 68 47 90 832, 951 • e-mail: export@relpol.com.pl