



## BETA 666/C20

Zero-Reset click-type torque wrench, in case, with sockets and extension bars



## Certifications and Standards



UNI EN ISO 6789

## Features

The 666/C20 kit guarantees reliable results and tidy tool management.

### OPTIMAL TOOL MANAGEMENT

the robust drawer protects and organises each component, also facilitating transport and handling.

### COMPLETE KIT FOR EVERY NEED

In addition to the torque wrench, sockets, extensions and related fittings are also included in the cassette for more efficient, faster and more versatile work.



### REVERSIBLE RATCHETS

72-tooth mechanism for fast and precise use of the wrench, ensuring a recovery angle of only 5°.



### DOUBLE GRADUATED SCALE

High scale visibility. Easily selectable setting with extremely precise increment.



### BIMATERIAL HANDLE

The ergonomic handle provides a solid and strong grip. Made of materials resistant to fuels, oils and industrial liquids

### Certifications and Standards



UNI EN ISO 6789

666/20: n. ZERO-RESET click-type torque wrenches □ 40÷200 Nm  
920A: n. 1/2" square drive hexagon sockets □ 13÷27 mm  
920/20÷920/22: n. 1/2" drive extension bar 75-125-255 mm  
920/15: n. 0 adaptor, 1/2" female and 3/8" male drives E 1/2 - B 3/8

### Coded items

|  | Art.    |
|-----------------------------------------------------------------------------------|---------|
| 006661020                                                                         | 666/C20 |

**Scan the QR Code to access the web tab**  
Specs, media and documentation in one click.

