

Cable Mini DisplayPort 1.2 male with screw > DisplayPort male 4K 60 Hz 1 m

Description

This Mini DisplayPort cable by Delock can be used to connect devices with DisplayPort interface, e.g. displays, projectors or TVs, to a PC or laptop. The triple shielded cable supports a resolution of up to Ultra HD (4K @ 60 Hz) and is downwards compatible to Full-HD 1080p.

The screw of the mini DisplayPort connector secures the connection and prevents accidental unplugging of the cable.



Item no. 83721

EAN: 4043619837212

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x mini DisplayPort male with screw >
 - 1 x DisplayPort male
- Input = mini DisplayPort; Output = DisplayPort
- Screw type: #4-40, thread type UNC, thread class 3A, American Standard Screw
- DisplayPort 1.2 specification
- Pin 20 not connected
- Cable gauge: 32 AWG
- Cable diameter: ca. 5.5 mm
- Contacts gold-plated
- 2 x ferrite core
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gb/s
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- One free mini DisplayPort female

Package content

- Mini DisplayPort cable

Images



General

Specification:	DisplayPort 1.2
----------------	-----------------

Interface

Connector:	1 x mini DisplayPort 20 pin male 1 x DisplayPort male
------------	--

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Ferrite core:	2 x
Pin finishing:	gold-plated
Cable gauge:	32 AWG
Screw type:	#4-40 UNC
Length:	1 m
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de