

USB Type-C™ SDHC / SDXC UHS-II / MMC Single Slot Card Reader

Description

This single slot card reader by Delock reads and writes SD and MMC memory cards. It can be connected to the USB Type-C™ port of a computer, tablet or smartphone. The supported SD UHS-II memory cards allow fast data transfer.



Item no. 91498

EAN: 4043619914982

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x SuperSpeed USB (USB 3.1 Gen 1) USB Type-C™ male >
 - 1 x SD slot
- Chipset: Realtek RTS5329
- Supports memory:
 - up to 2 TB
 - SD 3.0 (UHS-I), SD 4.0 (UHS-II)
- Data transfer rate:
 - USB 3.1 Gen 1 up to 5 Gbps
 - SD read up to 250 MB/s, write up to 185 MB/s
- Dimensions (LxWxH): ca. 40.2 x 34.4 x 9.6 mm
- Hot Swap, Plug & Play
- Supports following memory cards:
 - Secure Digital (SD), SDHC UHS-I, SDHC UHS-II, SDXC UHS-I, SDXC UHS-II, Mini SD*, Mini SDHC*, Mini SDXC*, Micro-SD*, Micro SDHC*, Micro SDXC*, T-Flash*, MultiMediaCard, MMCplus, MMCmobile*, RS-MMC*, MMCmicro*
 - *Adapter is required

System requirements

- Windows 7/7-64/8.1/8.1-64/10/10-64, Linux ex Kernel 2.6.x / Kernel 4.x.x, Mac ex OS 10.12.5, Android ex 7.1.2
- Device with a free USB Type-C™ port or with a free Thunderbolt™ 3 port

Package content

- USB Type-C™ Card Reader
- User manual

Images



General

Function:	Hot Swap Plug & Play
Specification:	USB 5 Gbps
Supported memory card:	Micro SD Micro SDHC Micro SDXC SD T-Flash MMCmicro SD UHS-I SD UHS-II MMC MMC plus RS-MMC MMCmobile Mini SD Mini SDHC SDHC UHS-I SDHC UHS-II SDXC UHS-I SDXC UHS-II Mini SDXC

Interface

Connector 1:	1 x USB 5 Gbps USB Type-C™ male
Connector 2:	1 x SD slot

Technical characteristics

Chipset:	Realtek RTS5329
Data transfer rate:	USB 5 Gbps

Physical characteristics

Housing material:	Aluminium
Length:	40.2 mm

Width:	34.4 mm
Height:	9.6 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de