

USB 10 Gbps Cable USB Type-C™ male to male PD 3.0 60 W E-Marker 1 m coaxial

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port. The coaxial conductors allow an interference-free data transfer with up to 10 Gbps.



Item no. 85207

EAN: 4043619852079

Country of origin: China

Package: Zip poly bag


Technical details

- Connectors:
 - 1 x USB 10 Gbps USB Type-C™ male
 - 1 x USB 10 Gbps USB Type-C™ male
- Chipset: Cypress E-Marker
- Cable gauge:
 - 30 + 32 AWG data line
 - 24 + 34 AWG power line
- Output current: up to 3 A
- Cable diameter: ca. 5 mm
- Conductors: 8 x coaxial for SuperSpeed USB, 1 x Twisted Pair for USB 2.0
- Data transfer rate up to 10 Gbps
- Colour: black
- Length incl. connectors: ca. 1 m

Package content

- USB cable

Images



General

| | |
|----------------|----------------------|
| Specification: | USB 10 Gbps |
| Style: | both sides identical |

Interface

| | |
|--------------|----------------------------------|
| Connector 1: | 1 x USB 10 Gbps USB Type-C™ male |
| Connector 2: | 1 x USB 10 Gbps USB Type-C™ male |

Technical characteristics

| | |
|---------------------|------------------|
| Chipset: | Cypress E-Marker |
| Data transfer rate: | 10 Gbps |
| Maximum current: | 3 A |

Physical characteristics

| | |
|-----------------|--|
| Pin finishing: | gold-plated |
| Conductors: | 1 x Twisted Pair 8 x coaxial |
| Cable gauge: | 30 AWG data line 32 AWG data line 24 AWG power line 34 AWG power line |
| Length: | 1 m |
| Colour: | black |
| Cable diameter: | 5 mm |

Manufacturer information

| | |
|-------------|-------------------|
| Street | Beeskowdamm 13/15 |
| Postal code | 14167 |
| City | Berlin |
| Country | Deutschland |
| E-Mail | info@delock.de |
| Website | www.delock.de |