

DIGITUS® Mobile workstation with individual height adjustment

DA-90374

EAN 4016032457435



Mobile Workstation (Monitor Mount, PC Holder) max. 8 kg load, 32" screen max., black

The mobile workstation offers enough space for a monitor, keyboard/mouse and PC with flexible working height adjustment. You can move your workstation to whatever place thanks to 4 maneuverable casters. Absolute flexibility. The cart is ideal for constantly changing workstations such as workshops, medical practices, warehouses, production facilities, etc. Set up a workstation that can be freely moved and individually adjusted to the working height by many people despite different body height. When selecting the bracket, please only consider the VESA size and check the weight and size of your monitor for compatibility. The PC holder has an adjustable width and can be adapted to any model.

Mobile workstation with bracket for mounting a monitor, keyboard/mouse and PC with flexible height adjustment

- Supported monitor sizes: 17" - 32"
- VESA mounting dimensions: 75 x 75, 100 x 100
- Tilt angle: -15° to +15°

- Swiveling: 360° (fixed adjustable)
- Monitor rotation: 360°
- Load capacity of monitors: max. 8 kg
- Keyboard tray load capacity: max. 2 kg
- PC load capacity: max. 10 kg
- All trays can be adjusted in height
- PC holder with adjustable width: 122 to 212 mm
- Integrated cable guide
- Solid metal with high quality powder coating
- Dimensions: L 50 x W 49.5 x H 178 cm
- Weight: 10.3 kg
- Cable management included

Attributes

- Style: PC Workstation

Package contents

- 1x mobile cart, sit-stand workstation, height adjustable
- 1x installation instructions

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	13.40	52.50	108.00	17.00	96,390.00
Packaging Unit Inside	1	13.40	52.50	108.00	17.00	96,390.00
Packaging Unit Single	1	13.40	52.50	108.00	17.00	96,390.00
Net single without Packaging	1	10.73	52.50	108.00	17.00	96,390.00

More images:



Safety notes

- Please read the entire manual before starting assembly and installation. Please contact your local dealer if you have any questions about the instructions or warnings.
- CAUTION: Use with products that exceed the permitted weight may result in damage or possible injury.
- Brackets should be fitted in accordance with the installation instructions. Incorrect installation can result in damage or injury.
- Use safety equipment and suitable tools. The product should only be installed by specialists.
- The load-bearing surfaces should be able to safely withstand the entire weight of appliances and all additional components.
- Only use the installation screws supplied and DO NOT TIGHTEN the screws TOO TIGHT.
- This product contains small parts that can cause a choking hazard if swallowed. Keep these parts away from children.
- Only use this product indoors. Using the product outdoors can lead to injuries and damage.
- IMPORTANT: Before installation, please check all components received against the components list. If parts are damaged or missing, ask your local dealer for replacement parts.

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schüffel 3
Lüdenscheid, Germany
<https://www.assmann.com>

info@assmann.com