


Film, Metallized Paper, Safety, KEMET, PME278/P278, 0.1 uF, 20%, 1,000 V, 440 V, 110C, Lead Spacing = 25.4mm



General Information	
Dielectric:	Metallized Paper
Style:	Radial
Supplier:	KEMET
Series:	PME278/P278
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
Construction:	Molded
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart). SRF= 3.9 MHz

Dimensions	
L	30.5mm MAX
H	19mm MAX
T	12.1mm MAX
S	25.4mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Specifications	
Capacitance:	0.1 uF
Capacitance Tolerance:	20%
Voltage DC:	1000 VDC
Voltage AC:	440 VAC
Temperature Range:	-40/+110C
Rated Temperature:	110C
Dissipation Factor:	1.3% 1kHz
Insulation Resistance:	12 GOhms
Max dVdt:	600 V
Safety Class:	X1

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	100