

DisplayPort 1.2 cable female to female panel-mount 4K 60 Hz 1 m

Description

This cable by Delock can be used to extend a DisplayPort connection and to connect various devices. The female port can be attached with two screws, e.g. to a slot bracket, a cable duct or an enclosure with the corresponding opening. In this way, it is possible to install a DisplayPort connector in an easily accessible position.



Item no. 87100

EAN: 4043619871001

Country of origin: China

Package: Box

Technical details

- Connectors:
 - 1 x DisplayPort female >
 - 1 x DisplayPort female panel-mount
- DisplayPort 1.2 specification
- Pin 20 is connected (supports 3.3 V)
- Screw type: M3
- Screw distance: 27 mm
- Cable gauge: 28 AWG
- Cable diameter: ca. 7 mm
- Copper conductor
- Triple shielded cable
- Contacts gold-plated
- Transmission of audio and video signals
- Data transfer rate up to 21.6 Gbps
- Resolution up to 3840 x 2160 @ 60 Hz
(depending on the system and the connected hardware)
- Supports HDR
- Supports HDCP 1.4 and 2.2
- Colour: black
- Length incl. connectors: ca. 1 m

System requirements

- A free DisplayPort interface

Package content

- DisplayPort panel-mount cable
- 2 x screw

Images



General

Specification:	DisplayPort 1.2 HDCP 1.4 HDCP 2.2 HDR
Style:	both sides identical

Interface

Connector 1:	1 x DisplayPort female
Connector 2:	1 x DisplayPort female

Technical characteristics

Data transfer rate:	21.6 Gbps
Maximum screen resolution:	3840 x 2160 @ 60 Hz

Physical characteristics

Pin finishing:	gold-plated
Conductor material:	copper
Cable gauge:	28 AWG
Screw distance:	27 mm
Screw type:	M3
Shielding:	triple
Length:	1 m
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de