



EMPTY ENCLOSURE

GEOS-L 3030-22-o



GEOS-L 3030-22-o

Empty enclosure

300 x 300 x 226 mm

Article number: 70073301

Empty enclosure - Industrial Quality -, suitable for installation in harsh environments and unprotected exterior areas, Base: glass fibre reinforced polycarbonate, Grey, similar to RAL 7035, Cover: Polycarbonate

with grey cover



Technical data

Measures

Width:	300 mm
Length:	300 mm
Height:	226 mm
Inner height:	204 mm
Inner width:	271 mm
Inner length:	271 mm

Material:

material:	Polycarbonate
Box:	polycarbonate, glass fiber-reinforced
Cover:	Polycarbonate
Sealing:	Elastomer
Cover screw:	polyamide, fiberglass-reinforced

Accessory

SRS 60-90 - Screw clamp set

GEOS MPI-3030 - Mounting plate

GEOS MPS-3030 - Mounting plate

GEOS-L EP-3030 - Mounting plate

GEOS MH-22 - Mounting holder

GEOS-L TW 30-22 - Partition wall

GEOS NS35-250 - Standard rail

GEOS ABL-10 - External fixing lug

GEOS ABL-40 - External fixing lug

BEL Air M40 - Ventilation element set

LFR M40 - Hole cutter

GEOS MSS-30 - Mast clamp set

SRS 90-150 - Screw clamp set

SRS 150-210 - Screw clamp set

GEOS DP-3030 - Design plate



EMPTY ENCLOSURE

GEOS-L 3030-22-o

Other attributes

weatherproof:	Yes
Combustion behaviour acc. to UL 94:	V-2 acc. UL 94
Combustion behaviour to UL 50 / UL 746C:	5VA nach UL 50 / UL 746C
Combustion behaviour acc. to VDE:	960°C acc. VDE 0471/ EN 60695
Ingress protection:	IP66/IP67 acc. EN 60529 / DIN VDE 0470-1
Impact resistance:	IK09 acc. DIN EN 50102 / VDE 470 segment 100
Color:	Grey
Rated insulation voltage AC:	1000 V
Rated insulation voltage DC:	1500 V

Environmental attributes

Ambient temperature (min.):	-35 °C
Ambient temperature (max.):	80 °C
Ambient temperature (24 h):	60 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%