

Coaxial USB 40 Gbps cable USB PD 3.1 240 W 1 m

Description

This USB cable by Delock enables the connection of various devices, such as smart phones, monitors, external enclosures and docking stations, via a USB Type-C™ or Thunderbolt™ 3 port of a PC or laptop. The cable supports the transfer of USB as well as DisplayPort and PCI Express data.

USB 40 Gbps

The cable enables data transfer rates up to 40 Gbps when connecting compatible devices. Of course, USB 3.2 or USB 2.0 devices can also be connected.

Connect DisplayPort monitors

The Delock cable supports DisplayPort 1.4a as well as DisplayPort 2.0 Alternate Mode, enabling the connection of DisplayPort monitors with a screen resolution up to 8K 30 Hz.

USB Power Delivery (USB PD 3.1) support up to 240 watt
Support for the Extended Power Range resp. USB Power Delivery 3.1 standard means that connected devices can be supplied with power, up to 240 W (48 V / 5 A) is possible.



Item no. 81706

EAN: 4043619817061

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors: 2 x USB 40 Gbps USB Type-C™ male
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3
- Chipset: E-Marker
- Cable gauge: 30 AWG
- Cable type: coaxial
- Cable diameter: ca. 4.8 mm
- Triple shielded cable
- Contacts gold-plated
- Data transfer rate up to 40 Gbps
- Display resolution up to:
7680 x 4320 @ 30 Hz
3840 x 2160 @ 144 Hz
(depending on the system and the connected hardware)
- Supports HDR10
- Supports HDCP 1.4 and 2.3
- Supports PCI Express 3.0 protocol
- Supports DisplayPort 1.4a protocol

- Supports DisplayPort Alt Mode 2.0
- Dual channel, bi-directional data transfer
- Supports Extended Power Range (EPR)
- USB Power Delivery (USB PD 3.1) support up to 240 watt (48 V / 5 A)
- Colour: black
- Length incl. connectors: ca. 1 m

Package content

- USB 40 Gbps cable

General

Specification:	HDCP 1.4 HDCP 2.3 HDR10 PCI Express 3.0 Thunderbolt™ 3 USB 2.0 USB Power Delivery 3.1 DisplayPort 1.4a USB 3.2 DisplayPort Alt Mode 2.0 Extended Power Range (EPR)
Style:	both sides identical

Interface

Connector 1:	1 x USB 40 Gbps USB Type-C™ male
Connector 2:	1 x USB 40 Gbps USB Type-C™ male

Technical characteristics

Chipset:	E-Marker
Maximum screen resolution:	7680 x 4320 @ 30 Hz 3840 x 2160 @ 144 Hz

Physical characteristics

Cable category:	coaxial
Cable length incl. connectors:	1 m
Pin finishing:	gold-plated
Cable gauge:	30 AWG
Shielding:	triple
Colour:	black
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de