

USB 40 Gbps FPC Flat Ribbon Cable USB Type-C™ to USB Type-C™ 15 cm PD 3.0 100 W E-Marker

Description

This USB cable by Delock enables the connection between a device with a USB Type-C™ connector and a PC or a laptop equipped with a free USB Type-C™ port.

Ultra flexible cable

The cable is characterized by its special construction. Instead of normal copper wires there is a flexible circuit board inside the cable, which is also called FPC (Flexible Printed Circuit). This makes the cable extremely flexible and yet robust. It is particularly suitable for charging smartphones via a power bank on the go.

USB4™ 40 Gbps

The cable enables data transfer rates up to 40 Gbps when connecting USB4™-compatible devices. Of course, USB 3.2 or USB 2.0 devices can also be connected.



Item no. 80099

EAN: 4043619800995

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors: 2 x USB 40 Gbps USB Type-C™ male
- Downwards compatible to USB 3.2, USB 2.0 and Thunderbolt™ 3
- Chipset: Cypress E-Marker
- FPC (Flexible Printed Circuit) flat ribbon cable
- Contacts gold-plated
- Cable thickness: ca. 3 mm
- Data transfer rate up to 40 Gbps
- USB Power Delivery (USB PD 3.0) support up to 100 watt (20 V / 5 A)
- Colour: black / grey
- Length incl. connectors: ca. 15 cm

System requirements

- USB cable

Images



General

Specification:	USB 40 Gbps USB Type-C™
Style:	Flat cable both sides identical

Interface

Connector 1:	1 x USB Type-C™ male
Connector 2:	1 x USB Type-C™ male

Technical characteristics

Chipset:	E-Marker
Data transfer rate:	40 Gbps
Maximum power:	100 W
Maximum current:	5 A
Voltage:	20.0 V

Physical characteristics

Cable category:	Flat cable
Pin finishing:	gold-plated
Length:	15 cm
Colour:	grey black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de