

Delock Cable mini DisplayPort 1.2 male with screw > DVI male 4K Active black 1 m

Description

This cable enables you to connect a DVI monitor through a free mini DisplayPort interface. The cable supports a resolution up to Ultra HD (4K) and is backward compatible to Full-HD 1080p. The screw of the mini DisplayPort connector secures the connection and prevents accidental unplugging of the cable.



Item no. 83725

EAN: 4043619837250

Country of origin: China

Package: Zip poly bag

Technical details

- Connector:
mini DisplayPort 20 pin male with screw >
DVI-D (Dual Link) 24+1 male
- Input = mini DisplayPort; Output = DVI
- Screw type: #4-40, thread type UNC, thread class 3A, American Standard Screw
- Chipset: Parade PS171
- DisplayPort 1.2 specification
- Cable gauge: 32 AWG
- Cable diameter: ca. 5.5 mm
- Gold-plated connector
- Active cable, for graphics cards with DP and DP++ output
- Supports a resolution up to 4K (4096 x 2160 pixel @ 24 Hz or 3840 x 2160 pixel @ 30 Hz) - depending on the system and the connected hardware
- Supports HDCP 1.3
- Supports Eyefinity
- 2 x ferrite core
- Cable length: ca. 1 m (incl. connector)
- Colour: black
- OS independent, no driver installation necessary

System requirements

- A free mini DisplayPort female port

Package content

- Cable mini DisplayPort to DVI

Images



General

Specification:	DisplayPort 1.2 HDCP 1.3
----------------	-----------------------------

Interface

Connector 1:	1 x mini DisplayPort male
Connector 2:	1 x DVI 24+1 male with screws

Technical characteristics

Chipset:	Parade PS171
Maximum screen resolution:	3840 x 2160 @ 30 Hz 4096 x 2160 @ 24 Hz

Physical characteristics

Ferrite core:	2 x
Pin finishing:	gold-plated
Cable gauge:	32 AWG
Screw type:	#4-40 UNC
Length:	1 m
Colour:	black
Cable diameter:	5.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de