

Antenna Cable FAKRA C plug to MHF® I plug 1.13 - 20 cm 1 prepunched hole

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.



Item no. 90727

EAN: 4043619907274

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x FAKRA C plug
 - 1 x MHF® I plug
- FAKRA C: RAL 5005 Signal blue
- Impedance: 50 Ohm
- Cable type: 1.13
- Cable type: coaxial
- Cable diameter: ca. 1.13 mm
- Cable attenuation: 3.2 dB @ 2.4 GHz per meter
- Smallest bending radius: 4.5 mm
- Mounting plate: steel
- 1 prepunched hole for mounting
- Thread type: M3
- Cable length without connectors: ca. 20 cm
- Dimensions (LxWxH): ca. 17 x 12 x 9 mm

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x FAKRA C plug
Connector 2:	1 x I-PEX Inc., MHF® I plug

Physical characteristics

Cable type:	1.13
Cable length:	20 cm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

