


Optical Fiber Cable LC Duplex to LC Duplex Multi-mode OM4 25 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.



Item no. 80154

EAN: 4043619801541

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
1 x LC Duplex
1 x LC Duplex
- Ceramic ferrule with dust protection
- Multi-mode OM4 cable
- Fibre: 50/125 µm
- Return loss: 35 dB
- Smallest bending radius: 25 mm
- Cable diameter: ca. 2.0 mm
- LS0H (halogen-free)
- Operating temperature: -20 °C ~ 70 °C
- Colour: violet
- Cable length: ca. 25 m

Package content

- Optical fiber cable

General

Specification:	OM4
Style:	both sides identical

Interface

Connector 1:	1 x LC Duplex male
Connector 2:	1 x LC Duplex male

Technical characteristics

Operating temperature:	-20 °C ~ 70 °C
------------------------	----------------

Physical characteristics

Cable colour:	violet
Cable length incl. connectors:	25 m
Smallest bending radius:	25 mm
Cable diameter:	2 mm
Cable jacket material:	LSOH (halogen-free)

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

