





REV.	ECN NO.	DATE	SIGN	DESCRIPTION
E	C210561	2021/04/16	Vicky	 X2
F	C210977	2021/06/23	Vicky	 X1
G	C221877	2022/12/13	Ruru	 X1

MSDP-XXBFFC-SL700I
XX: No. Of Pin



4P

Pin Assignments Front View



Note:

- * RoHS Compliant
- *  Important Dimension
- *  Waterproof rate: IP67, mated
- * Connector

Housing: Thermoplastic, Black
Pin: Copper alloy, Gold plated
Extension Nut: Thermoplastic, Black
Nut: Thermoplastic, Black

- *  O-Ring: Rubber, Gray
- * Clamp Ring: Thermoplastic, Black
- * Sealing Nut: Thermoplastic, Black
- * Seal: Rubber, Gray, OD: $\varnothing 4.0\text{mm} \sim \varnothing 8.0\text{mm}$
- * Applicable wire gauge: 20AWG~24AWG
- * One set unassembled in one pe bag

UNIT: mm				TITLE N SEN, MI2 D -PLASTIC, SCREW 				
TOLERANCE			CABLE W/O SR, F, F, FI/PANEL CRIMP					
.X	±0.25		SCALE	Free	SIZE	A4	SHEET	1 OF 1
.XX	±0.1		REV.	G	WC-REV.	.0	QC: Inspection item	
.XXX	±0.05							
ANGLES		±1°						

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Xiaofeng	2019/12/17
DWG NO	CHECKED BY	DATE
MSDP-XXBFFC-SL7001	Li-Feng	2019/12/17
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2019/12/17