

Desktop Patch Panel 12 Port Cat.6 grey

Description

This patch panel by Delock can be mounted e.g. on a wall. At the LSA blocks you can install up to 12 network cables with a punch down tool.



Item no. 87292

EAN: 4043619872923

Country of origin: China

Package: White Box


Technical details

- Connectors:
external: 12 x RJ45 jack
internal: 12 x LSA blocks
- Wall mounting
- Shielded
- Cat.6
- TIA-568A/B pinout
- Cable diameter up to 0.644 mm (22 - 24 AWG)
- For solid or stranded wire
- Metal housing
- Colour: light grey RAL 7035
- Dimensions (WxHxD): ca. 218 x 44.2 x 108 mm

Package content

- Patch Panel
- Installation manual
- 12 cable ties
- 2 wallmount screws
- Insertion Tool und Cable Stripper Delock 18411

Images



General

Suitable for conductor gauge:	22 - 24 AWG
Mounting type:	wall

Interface

External:	12 x RJ45 jack
Internal:	12 x LSA block

Technical characteristics

Category:	Cat.6
-----------	-------

Physical characteristics

Housing colour:	light grey
Housing material:	metal
Shielding:	shielded
Depth:	108.0 mm
Width:	218 mm
Height:	44.2 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

