


Optical Fiber loopback Adapter LC / UPC singlemode blue

Description

This loopback adapter by Delock can be used for testing purposes and for testing fiber optic connections. With the loopback, the transmission capability of the optical fibers can be measured.



Item no. 86924

EAN: 4043619869244

Country of origin: China

Package: Zip poly bag


Technical details

- Connector:
1 x LC Duplex male
- Singlemode UPC cable
- Fibre: 9/125 µm
- Return loss: 55 dB
- Zirconia ferrule with dust protection cap
- Cable diameter: ca. 2 mm
- Operating temperature: -20 °C ~ 70 °C
- Colour: blue / yellow
- Cable jacket material: PVC
- Dimensions (LxWxH): ca. 60 x 20 x 11 mm

Package content

- Optical fiber adapter loopback

Images



General

Specification:	UPC
----------------	-----

Interface

Connector:	1 x LC Duplex male
------------	--------------------

Technical characteristics

Operating temperature:	-20 °C ~ 70 °C
------------------------	----------------

Physical characteristics

Material:	PVC
Length:	60 mm
Width:	20 mm
Height:	11 mm
Colour:	blue yellow
Cable diameter:	3 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

