




FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人

SPECIFICATIONS:

1.SWITCH RATING: 2A/36VDC.

2.MECHANICAL LIFE: ≥1,000,000 cycles(MOMENTARY),
≥500,000 cycles(LATCHING).

3.ELECTRICAL LIFE: ≥50,000 cycles.

4.INITIAL CONTACT RESISTANCE: ≤50mΩ.

5.INSULATION RESISTANCE: ≥1000MΩ(500VDC).

6.POWER-FREQUENCY WITHSTAND VOLTAGE: 1,500V, RMS 50Hz, 1min.

7.OPERATING TEMPERATURE: -25℃~ +55℃(NO FREEZING, KEEP THE AIR FLOWING AROUND PUSHBUTTON).

8.TORQUE: ABOUT 0.3N·m APPLIED TO NUT.

9.OPERATING FORCE: ABOUT 2.5N.


10.OPERATING TRAVEL: ABOUT 2.4mm.

11.FRONT PANEL PROTECTION DEGREE: IP65(IP67 CAN BE CUSTOMIZED); IK07.

12.TERMINAL TYPE: PIN TERMINAL(2X0.5mm).

13.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

14.COMPLIANT WITH RoHS.



MATERIALS:

1.CONTACT: SILVER ALLOY.

2.BUTTON: STAINLESS STEEL.

3.BODY: STAINLESS STEEL.

4.BASE: PA.

PART NUMBER:ONPOW6312C-10■/J/S/※

■	OPERATION MODE
NO LETTER	MOMENTARY
Z	LATCHING
※	PROTECTION DEGREE
NO LETTER	IP65
FP	IP67(CUSTOMIZED)

BRAND 品牌		红波按钮制造有限公司					
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.					
TITLE 名称	ONPOW63 SERIES ANTI-VANDAL PUSH BUTTON			UNIT 单位	mm		
DWG NO. 图号	ONPOW6312C-10(不带灯)		SCALE 比例	2 : 1	SIZE 图纸	A4	
FILE NAME 档案名称	ONPOW6312C .DWG	DRAWN 制图	HCP 2025/08/04	SHEET 张	1/1	REV. 版本	V1.0