


# Optical Fiber loopback Adapter LC / OM3 Multi-mode beige

## Description

This loopback adapter by Delock can be used for testing purposes and for testing fiber optic connections. With the loopback, the transmission capability of the optical fibers can be measured.



**Item no. 86931**

EAN: 4043619869312

Country of origin: China

Package: Zip poly bag

## Technical details

- Connector:
  - 1 x LC Duplex male
- Multi-mode OM3 cable
- Fibre: 50/125 µm
- ~~Is not a fiber~~ Is not a fiber with dust protection cap
- Cable diameter: ca. 2 mm
- Operating temperature: -20 °C ~ 70 °C
- Colour: beige / aqua
- Cable jacket material: PVC
- Dimensions (LxWxH): ca. 60 x 20 x 11 mm

## Package content

- Optical fiber adapter loopback

## Images



## General

|                |     |
|----------------|-----|
| Specification: | OM3 |
|----------------|-----|

## Interface

|            |                    |
|------------|--------------------|
| Connector: | 1 x LC Duplex male |
|------------|--------------------|

## Technical characteristics

|                        |                |
|------------------------|----------------|
| Operating temperature: | -20 °C ~ 70 °C |
|------------------------|----------------|

## Physical characteristics

|                 |               |
|-----------------|---------------|
| Material:       | PVC           |
| Length:         | 60 mm         |
| Width:          | 20 mm         |
| Height:         | 11 mm         |
| Colour:         | aqua<br>beige |
| Cable diameter: | 3 mm          |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

