

ART P1230 Extension Cord with Switch

3 sockets | white | 5 m | 16 A | 3 x 1.5 mm2

ART P1230 is a standard 230 V extension cord for safe, convenient power distribution at home, in the office and at workstations. It provides three grounded sockets, a practical switch and a power indicator.

Key features		Technical specification			
3 grounded sockets Power up to three devices at the same time.	Integrated switch Turn connected devices on or off with one switch.	Brand	ART	Manufacturer code	P1230
		Product type	230 V electrical extension cord	Cable length	5 m
Power indicator Shows connection to the mains supply.	16 A / 3680 W For common household and office equipment within the rated load.	Cable	H05VV-F, 3 x 1.5 mm2	Number of sockets	3 two-pole sockets with protective earth contact
		Socket rating	16 A / 250 V	Max. load	3680 W
3 x 1.5 mm2 cable H05VV-F cable for everyday use.	Self-extinguishing housing Certified self-extinguishing plastic improves product safety.	Rated voltage	230 V	Frequency	50-60 Hz
		Rated current	16 A max.	Power switch	Yes
		Power indicator	Yes	Housing material	Certified self-extinguishing plastic
		Electric shock protection	Protective pins of sockets connected to protective conductor	Colour	White
		Product dimensions	L220 x W49 x H42 mm	Product weight	690 g
		Warranty	36 months	Safety / conformity mark	CE
		Market approval	Approved for sale in Poland	Country of origin	Malaysia
		CN code	8544 42 90		

Positioning note: This product belongs to the ART electrical extension cord range. It is a standard extension cord with switch and power indicator, not an SPD surge protective device.