

Optical fiber cable LC Duplex to LC Duplex with protective cap multi-mode OM2 IP68 dust and waterproof 3 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.

IP68 dust and waterproof

The waterproof screw connection can be attached, for e.g. to a housing with a suitable cut-out and is ideal for outdoor use.



Item no. 87888

EAN: 4043619878888

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x LC Duplex
 - 1 x LC Duplex
- Multi-mode OM2 cable
- Fibre: 50/125 µm
- Ceramic ferrule with dust protection
- Cable diameter: ca. 7.5 mm
- Cable jacket material: PVC
- Colour: orange
- Length incl. connectors: ca. 3 m

Package content

- Optical fiber cable

Images



General

Style:	both sides identical
--------	----------------------

Interface

Connector 1:	1 x LC Duplex male
Connector 2:	1 x LC Duplex male

Physical characteristics

Material:	PVC
Length:	3 m
Colour:	orange
Cable diameter:	7.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

