

Cable USB 2.0 Extension, active 10 m

Description

This USB 2.0 cable by Delock can be connected to an active USB port and enables an extension of 10 m. By connecting of an additional 10 m extension cable you can extend your USB port up to 20 m.



Item no. 82446

EAN: 4043619824465

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x USB 2.0 Type-A female
- Chipset: FE 1.1
- For connection to an active USB port
- Cable gauge:
 - 28 AWG data line
 - 22 AWG power line
- Data transfer rate up to 480 Mbps
- Extension up to 2 x 10 m cables
- Connectors: gold-plated
- Power: up to max. 500 mA
- Cable length: ca. 10 m

System requirements

- Linux Kernel 3.2 or above
- Mac OS 10.9 or above
- Windows Vista/Vista-64/7/7-64/8.1/8.1-64/10/10-64/11
- PC or laptop with a free active USB Type-A port

Package content

- USB 2.0 extension cable 10 m

Images



General

Specification:	USB 2.0
----------------	---------

Interface

Connector 1:	1 x USB 2.0 Type-A female 1 x USB 2.0 Type-A male
--------------	--

Technical characteristics

Chipset:	FE1.1
Data transfer rate:	480 Mbps
Maximum current:	500 mA

Physical characteristics

Connector finishing:	gold-plated
Cable gauge:	28 AWG data line 22 AWG power line
Length:	10 m

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de