


Keystone Module RJ45 jack to LSA Cat.6A 180° toolfree metal

Description

This module by Delock can be used to connect a network cable and is suitable for easy snap-in mounting in various holders, such as keystone patch panels, face plates or surface-mount boxes.



Item no. 87036

EAN: 4043619870363

Country of origin: China

Package: Zip poly bag



Technical details

- Connectors:
 - 1 x RJ45 jack (8P/8C) >
 - 1 x LSA 180° (toolfree)
- Cat.6A specification
- Shielded (STP)
- Module end with cable gland
- TIA-568A/B pinout
- For solid or stranded wire (26 - 22 AWG)
- For cable diameter from 6.0 - 8.5 mm
- For Keystone ports with 19.2 x 14.9 mm
- Material: zinc die cast
- Dimensions (LxWxH): ca. 47.4 x 25.0 x 16.9 mm

Package content

- Keystone module
- Cable manager
- Module end

Images



General

Specification:	Cat. 6A
----------------	---------

Interface

Connector 1:	1 x RJ45 jack
Connector 2:	1 x LSA 180° (toolfree)

Physical characteristics

Cable gauge:	26 - 22 AWG
Material:	zinc die cast
Shielding:	shielded
Length:	47.4 mm
Width:	25.0 mm
Height:	16.9 mm
Cable diameter:	6.0 - 8.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

