

# DIGITUS® CAT 6 Connection module for Twisted Pair Cables - 5 pieces

DN-93903-5

EAN 4016032494829



## connection module for twisted pair cables LSA, shielded, CAT 6, 5 pieces

The DIGITUS® Connection module is for the purpose of connecting or extension of Twisted Pair Cables.

### Future-oriented standards and high-end quality for your network.

- Transmission properties: Category 6
- Area of application: Up to 250 MHz, 1GBase-T
- Norms: ISO/IEC 11801 3rd Ed., EN 50173-1, EIA/TIA 568-C
- General properties:
- Suitable for installation in trunking, surface and flush mount
- Cable installation via LSA stripes, color-coded as per EIA/TIA 568 A & B
- Suitable for connection of installation cables - extension of cables, replacing of defect cable links
- Integrated strain relief for installation cables
- Suitable for cables with AWG 22-26 diameter
- Technical properties:
- Housing material: ABS UL-94V-0

- RJ45 female contact: Tinned phosphor bronze, 0.5 mm gold-plated contact
- RJ45 shielding: Tinned bronze
- LSA termination clamp: Krone LSA+, UL 94V-0, zinc plated phosphor bronze
- Conductor plate: FR4, UL 94V-0
- Physical properties:
- Operation temperature: -20° C to +70 °C (ISO/IEC 11801, EN 50173-1, ANSI/TIA/EIA 568 C)
- IDC wire size: 22 – 26 AWG solid and stranded conductor
- Insulation resistance: > 500 MOhm
- Contact resistance: < 20 MilliOhm
- Dielectric strength: 1000 VDC (Contact/Contact), 1500 VDC (Contact/Ground)
- 5 pieces

### Attributes

- Category: CAT 6

## Logistics

|                              | Number (pcs) | Weight (kg) | Depth (cm) | Width (cm) | Height (cm) | cm³      |
|------------------------------|--------------|-------------|------------|------------|-------------|----------|
| Packaging Unit Carton        | 1            | 0.30        | 21.00      | 22.00      | 10.00       | 4,620.00 |
| Packaging Unit Inside        | 1            | 0.30        | 21.00      | 22.00      | 10.00       | 4,620.00 |
| Packaging Unit Single        | 1            | 0.30        | 21.00      | 22.00      | 10.00       | 4,620.00 |
| Net single without Packaging | 1            | 0.29        | 21.00      | 22.00      | 10.00       | 4,620.00 |

**More images:**



**Safety notes**

- Protect product from moisture
- Avoid antistatic charging when installing the product
- Observe the specifications of the raw cable manufacturer during installation

**EU responsible person**

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH  
Auf dem Schöffel 3  
Lüdenscheid, Germany  
<https://www.assmann.com>  
[info@assmann.com](mailto:info@assmann.com)