

SPECIFICATIONS :

1. SMA STRAIGHT PLUG, P/N:
FOR RG178 CABLE: RFCT-SMA022-M78.
FOR Ø1.13MM CABLE: RFCT-SMA011-M13.

2. COAXIAL CABLE, SEE P/N FOR DETAIL.

3. SMA RIGHT ANGLE BULKHEAD JACK WITH O-RING RATED TO IP67/68, GOLD PLATED, P/N:
FOR RG178 CABLE: RFCT-SMA073-F78 W/SILICONE O-RING OR RFCT-SMA073-F78-3 W/FLUOROSILICONE O-RING.
FOR Ø1.13MM CABLE: RFCT-SMA079-F13 W/SILICONE O-RING

ENVIRONMENTAL:

A. BULKHEAD MOUNTED CONNECTOR (RFCT-SMA073-F78/RFCT-SMA079-F13) RATED TO THE FOLLOWING SPECIFICATION:

i. IP6X - DUST TIGHT - NO PARTICLE INGRESS.

ii. IPX7 WATERPROOF FOR 30 MINUTES UP TO 1 METER UNDERWATER.

iii. IPX8 WATERPROOF FOR 48 HOURS AT 1 METER UNDERWATER.



HOW TO ORDER

CABLE 399 RF - X X X X - X - X - X

"L" LENGTH IN MM:
eg: 100MM = 0100
(MIN. 050-MAX.2000
STANDARD = 0100, 0150, 0200)
Tolerance: 50-200mm: ±5mm.
201-500mm: ±7mm.
>500mm: ±10mm.

O-RING MATERIAL OPTIONS:
BLANK = SILICONE, COLOR: RED (STANDARD)
F = FLUOROSILICONE, COLOR: BLACK

CABLE SIZE OPTIONS:
1 = RG178 CABLE, COLOR: BROWN
2 = Ø1.13MM CABLE, COLOR: GRAY

WASHER AND NUT OPTIONS:
BLANK = SEPARATELY PACKED (STANDARD)
A = ASSEMBLED WITH CONNECTOR

INTERNAL SEAL

IP RATED EVEN WHEN UNMATED