

DIGITUS® CAT 3 ISDN Patch Panel, unshielded, grey

DN-91325-1

EAN 4016032269007



CAT 3 ISDN Patch Panel, unshielded, 25-port RJ45, 8P4C, LSA, 1U, rack mount, grey, 482x44x109

The ISDN Patch Panels from DIGITUS® are available as 25- or 50-port version. With 1.5 mm galvanized cold-rolled steel they are perfectly suitable for 19" rack mounting.

Future-oriented standards and high-end quality for your network.

- Suitable for 483 mm (19") rack mount
- Suitable for cables with AWG 22-26 diameter
- Material housing: SECC, 1.5 mm electrogalvanized, cold-rolled steel acc. EN1.4301, UNS S30400, AISI 304 and LMSAD110
- RJ45 female, 8P4C
- Unshielded RJ45 jacks
- Material contacts: Phosphor bronze
- Contacts coating: Nickel, gold plated 0,3µ

- Cable installation via LSA strips, color coded according to EIA/TIA 568 A & B
- Material IDC Terminal: Phosphor bronze with 50 µ tin plated over 60 µ nickel plated
- Material PCB: FR4, UL 94V-0, multilayer 1.45 mm thickness
- Insertion force: 30 N
- Mating cycles: 750 (ISO/IEC 11801, IEC 60603-7-5)
- Operating temperature: -20°C ... +70°C
- Current carrying capacity: 1A at 50 °C
- Isolation resistance > 500MΩ
- Color: Grey (RAL 7035)


Attributes

- Color: light grey, RAL 7035
- Ports: 25
- Units: 1
- Category: CAT 3

Logistics

	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	10	14.46	53.50	32.00	28.00	47,936.00
Packaging Unit Inside	1	1.45	5.20	51.30	14.80	3,948.05
Packaging Unit Single	1	1.45	51.50	5.50	10.50	2,974.12
Net single without Packaging	1	1.34	51.50	5.50	10.50	2,974.12

More images:



Safety notes

- Protect product from moisture
- Avoid antistatic charging when installing the product
- Observe the specifications of the raw cable manufacturer during installation

EU responsible person

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH
Auf dem Schöffel 3
Lüdenscheid, Germany
<https://www.assmann.com>
info@assmann.com