

Cable Optical Fibre LC > LC Singlemode OS2 0.5 m

Description

This fiber optical cable by Delock can be used to connect different networking devices, e.g. a switch to a media converter.



Item no. 86545

EAN: 4043619865451

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
2 x LC Duplex
- Ceramic ferrule with dust protection
- Singlemode OS2 cable G657.A
- Fibre: 9/125 µm
- Cable diameter: ca. 2.0 mm
- LS0H (halogen-free)
- Operating temperature: -20 °C ~ 70 °C
- Colour: yellow
- Cable length: ca. 0.5 m

Package content

- Optical Fibre Cable

General

Specification:	OS2
Style:	both sides identical

Interface

Connector 1:	1 x LC Duplex
Connector 2:	1 x LC Duplex

Physical characteristics

Cable colour:	yellow
Cable length incl. connectors:	0.5 m
Cable diameter:	1.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

