

ART P1220 Extension Cord with Switch

3 sockets | white | 1.5 m | 16 A | 3 x 1.5 mm2

ART P1220 is a standard 230 V extension cord for safe, convenient power distribution at home, in the office and at workstations. It provides three grounded sockets, a practical switch and a power indicator.

Key features		Technical specification			
3 grounded sockets Power up to three devices at the same time. Integrated switch Turn connected devices on or off with one switch. Power indicator Shows connection to the mains supply. 16 A / 3680 W For common household and office equipment within the rated load. 3 x 1.5 mm2 cable H05VV-F cable for everyday use. Self-extinguishing housing Certified self-extinguishing plastic improves product safety.		Brand	ART	Manufacturer code	P1220
		Product type	230 V electrical extension cord	Cable length	1.5 m
		Cable	H05VV-F, 3 x 1.5 mm2	Number of sockets	3 two-pole sockets with protective earth contact
		Socket rating	16 A / 250 V	Max. load	3680 W
		Rated voltage	230 V	Frequency	50-60 Hz
		Rated current	16 A max.	Power switch	Yes
		Power indicator	Yes	Housing material	Certified self-extinguishing plastic
		Electric shock protection	Protective pins of sockets connected to protective conductor	Colour	White
		Product dimensions	L220 x W49 x H42 mm	Product weight	320 g
		Warranty	36 months	Safety / conformity mark	CE
		Market approval	Approved for sale in Poland	Country of origin	Malaysia
		CN code	8544 42 90		

Positioning note: This product belongs to the ART electrical extension cord range. It is a standard extension cord with switch and power indicator, not an SPD surge protective device.