


SKINDICHT® KU, KUS, KUK

SKINDICHT® KU, KUS, KUK, 玻璃纤维加强型聚酰胺缩径头确保最大机械稳定性, 带 PG 制连接螺纹



有空间需求

优势

允许使用连接螺纹比现有螺纹孔径更小的电缆夹套
加强型玻璃纤维, 达到最大机械应力

应用范围

机械设备
设备
罩壳

产品结构

PG 制连接螺纹

产品结构

SKINDICHT® KU with hexagon and flat design (1)

SKINDICHT® KUS with hexagon and larger height (2)

SKINDICHT® KUK with knurled heads (3)

SKINDICHT® KU, KUS, KUK

技术参数

分类 ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 类别描述: 电缆螺纹夹套

分类 ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

发货颜色:

RAL 7035 浅灰色

材料:

聚酰胺, 玻璃纤维加强

温度范围:

-40° C 至 +100° C

备注

照片和图像不能缩放, 也不能代表各自产品的详细图像。
价格为不含增值税与附加费的净价。对企业用户销售。



LAPP GROUP

产品信息

SKINDICHT® KU, KUS, KUK

物料编号	物料描述 / 尺寸
SKINDICHT® KU	
51730010	KU 11/7
52025100	KU 13,5/7
52025110	KU 16/9
52025120	KU 21/11
51730040	KU 21/13,5
52025130	KU 29/13,5
51730050	KU 29/16
52025140	KU 36/16
52025150	KU 36/21
52025050	KU 36/29
52025160	KU 42/21
52025170	KU 42/29
52025060	KU 42/36
52025180	KU 48/29
52025190	KU 48/36
52025070	KU 48/42
SKINDICHT® KUS	
52025040	KUS 9/7
51730060	KUS 11/9
51730070	KUS 13,5/11
51730080	KUS 16/13,5
SKINDICHT® KUK	
51730020	KUK 13,5/9
51730025	KUK 16 /9
51730030	KUK 16/11
51730035	KUK 21/13,5
51730090	KUK 21/16
51730100	KUK 29/21
51730110	KUK 36/29

Last Update (01.02.2018)

©2018 Lapp Group - 保留技术性变更

产品管理 <http://lappchina.lappgroup.com>

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16