

ART P1225 Extension Cord with Switch

3 sockets | white | 3 m | 16 A | 3 x 1.5 mm2

ART P1225 is a standard 230 V extension cord for safe, convenient power distribution at home, in the office and at workstations. It provides three grounded sockets, a practical switch and a power indicator.

Key features		Technical specification			
3 grounded sockets Power up to three devices at the same time.		Brand	ART	Manufacturer code	P1225
		Product type	230 V electrical extension cord	Cable length	3 m
Integrated switch Turn connected devices on or off with one switch.		Cable	H05VV-F, 3 x 1.5 mm2	Number of sockets	3 two-pole sockets with protective earth contact
		Socket rating	16 A / 250 V	Max. load	3680 W
Power indicator Shows connection to the mains supply.		Rated voltage	230 V	Frequency	50-60 Hz
		Rated current	16 A max.	Power switch	Yes
16 A / 3680 W For common household and office equipment within the rated load.		Power indicator	Yes	Housing material	Certified self-extinguishing plastic
		Electric shock protection	Protective pins of sockets connected to protective conductor	Colour	White
3 x 1.5 mm2 cable H05VV-F cable for everyday use.		Product dimensions	L220 x W49 x H42 mm	Product weight	490 g
		Warranty	36 months	Safety / conformity mark	CE
Self-extinguishing housing Certified self-extinguishing plastic improves product safety.		Market approval	Approved for sale in Poland	Country of origin	Malaysia
		CN code	8544 42 90		

Positioning note: This product belongs to the ART electrical extension cord range. It is a standard extension cord with switch and power indicator, not an SPD surge protective device.