

TUNGSRAM™

Innovation is our heritage
EST. 1896



5
kWh/1000h

A+
energy class

78
lumens/watt

LED GU10

LED Start GU10 5W(50) 830 35° TU

93118615

Product information

This new entry level range of highly competitive LED GU10 and R50 products consume only 3.5W and 5W respectively and offer a fantastic energy saving alternative to 50W and 35W Halogen GU10 lamps.

Application areas




Retail



Hospitality



Home



Product data

Product Code	93118615
Bulb Shape	PAR
Bulb Finish	Diffuse
Bulb Diameter [mm]	50
Nominal Length [mm]	53
Net weight per piece [g]	29
RoHS compliant	Yes
Brand	Tungsram
Cap/Base	GU10

Performance data

Nominal/ Rated Beam Angle [°]	35
Rated peak intensity in [Cd]	700
Weighted energy consumption [kWh/1000h]	5.0
Useful lumens (at 90° cone) [lm]	390
Rated efficacy [lm/W]	78
Energy efficiency class (EEC)	A+
Rated life L70/B50 [h]	15000
Nominal correlated colour temperature (CCT) [K]	3000
Nominal lumens [lm]	390
Colour Rendering Index (CRI) [Ra]	80

Electrical data

Nominal lamp power factor...	>0,5
Operating Temperature (MIN) [°C]	-20°C
Operating Temperature (MAX) [°C]	+40°C
Starting time (sec)	<0,5
Warm up time up to 60% of full light output	<1sec/instant
Number of switching cycles	50000
Dimming Capability	No
Nominal lamp voltage range [V]	220-240
Nominal power [W]	5

Logistic data

Shipment	Standard
DUN Code	15994100072604
EAN Code	5994100072607
Pack Quantity	8
Product status	Available

Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Product datasheet \(PDF\)](#)

[Datasheet \(PDF\)](#)

[Images \(HTTP\)](#)

[Doc documents Gen7 \(PDF\)](#)

[Doc documents Gen8 \(PDF\)](#)

[Datasheet \(FR\) \(PDF\)](#)