

# DIGITUS® CAT 6A modular couplers, shielded - 2 pieces

DN-93905-2

EAN 4016032495062



2x

**CAT6A modular coupler, full shielded RJ45 to RJ45, 2 pcs.**

Corresponds with requirements channel performance Class EA ISO/IEC 11801 for up to 500 MHz

- 2 x RJ-45 female
- Assignment: 1:1
- Shielded version
- Material enclosure: Brass sheet - shining Nickel plated
- Material PCB: FR4, 1.2 mm thickness

- Material contacts: Phosphor bronze
- Contacts coating: Nickel, gold plated 0.6 µ
- Mating cycles: ≥ 750
- Operating temperature: -10 °C ~+50 °C
- 2 pieces

**Attributes**

- Category: CAT 6A

**Logistics**

|                                 | Number<br>(pcs) | Weight<br>(kg) | Depth<br>(cm) | Width<br>(cm) | Height<br>(cm) | cm³   |
|---------------------------------|-----------------|----------------|---------------|---------------|----------------|-------|
| Packaging Unit Carton           | 1               | 0.10           | 5.00          | 5.00          | 2.00           | 50.00 |
| Packaging Unit Inside           | 1               | 0.10           | 5.00          | 5.00          | 2.00           | 50.00 |
| Packaging Unit Single           | 1               | 0.10           | 5.00          | 5.00          | 2.00           | 50.00 |
| Net single without<br>Packaging | 1               | 0.10           | 5.00          | 5.00          | 2.00           | 50.00 |

**More images:**

**Safety notes**

- Protect product from moisture
- Avoid antistatic charging when installing the product
- Observe the specifications of the raw cable manufacturer during installation

**EU responsible person**

EU based economic operator ensuring the product complies with the required regulations.

ASSMANN Electronic GmbH

Auf dem Schüffel 3

Lüdenscheid, Germany

<https://www.assmann.com>

[info@assmann.com](mailto:info@assmann.com)